




innovative
Sensor
Technology

MiniSens Pt100 class F0.15, with optimized ESD design



Small thin-film platinum 100 Ohm RTD ESD-optimized component with 10 mm platinum-cladded nickel wires

Benefits & Characteristics

- Excellent long-term stability
- Small dimensions
- Low self-heating
- Vibration and temperature shock resistant
- Fast response time
- ESD-optimized

Product Name: P0K1.161.6W.A.010

Nominal resistance: 100 Ω at 0 °C

Operating temperature range: -200 °C to +600 °C

TCR: Pt 3850 ppm/K

Chip size/dimensions: 1.6 x 1.2 x 0.6 mm

Tolerance/class: IEC 60751 F0.15 (IST AG reference class A)

Connection type: Pt/Ni-wire, Ø 0.2 mm

Wire length: 10 mm

Special: ESD optimized design (IEC/EN 61000-4-2)

Packaging: Blister

Product Old code: replaces product code 100138

Product code: 154366

Product details

Platinum Sensors

Innovative Sensor Technology IST AG platinum temperature sensors provide solutions for extreme temperature applications and are designed with the highest quality materials, allowing them to operate within a wide temperature range of -200 °C to +1000 °C. Standard IEC 60751 sensors are offered in class F0.3 (0.12 %), class F0.15 (0.06 %), F0.1 (0.04 %), and higher accuracies upon request. Our sensors are available in wireless (SMD) and wired configurations, and in sizes ranging from 0.75 mm to 10 mm (L), and 0.75 mm to 5.08 mm (W). Standard sensors can be customized with a variety of lead wire material, insulations, length, and configurations.

With many years of experience, iST also offers development of customer-specific applications in terms of sensor technology development and consultation. As part of the standard development process, we give support at the point of implementation - this way we ensure the best sensor solution for specific applications.

[More information on platinum temperature sensors](#)

Small dimensions

IST AG offers various sensor solutions for applications with limited space requirements.

MiniSens

iST MiniSens features the smallest footprint with dimensions of only 1.2 mm x 1.6 mm making the sensor an optimal solution for limited space applications. The MiniSens is available with accuracies of up to IEC 60751 F0.1 (IST AG reference class Y) and with

long directly welded wires. The sensor can be used in applications with an operation temperature range of up to +600 °C.

The MiniSens is also offered with a metallized backside enabling optimal thermal coupling.

SlimSens

The iST SlimSens sensor is specially developed for applications requiring sensors fitted into tubes with very small diameters. The SlimSens measures 0.8 mm x3 mm and is the optimal solution for applications with tube diameters from 1 mm. The SlimSens is available with accuracies of up to IEC 60751 F0.1 (IST AG reference class Y) and with long directly welded wires within various ohmic resistances. This Pt temperature sensor can be used in applications with an operation temperature range of up to +600 °C.

MiniSens Pt1000 class F0.15, lead-free > Details

ESD optimized design

To strengthen the stability of your assembled systems we are committed to the continued optimization and development of ESD-optimized temperature sensors.

With optimized design and new process technology we offer platinum temperature sensors with outstanding ESD resistance. The designs have been tested according to European Union Standards, the IEC/EN61000-4-2.

Thanks to a state-of-the art in-house ESD laboratory, we are able to test our sensors internally according to international standards.

[Download flyer for more information.](#)

Quality

Consistent with the well-known, high-quality standards in Switzerland, IST AG is certified according to ISO 9001:2015 (quality) and ISO 14001:2015 (environment).

Appropriate processes are part of our daily work. They are regularly audited and extended parallel to the growth of our company.

[> Read more](#)

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

10-49	CHF 7.39
-------	----------

50-99	CHF 5.87
-------	----------

100-150	CHF 5.19
---------	----------

Sklad: **434**