

FS7 EvaKit



Flow Demo Board with FS7 Sensor: evaluation electronics for anemometric (thermal) flow sensors

Ideal for testing FS7 sensors in your application.

Product Name: Flow Eval Board FS/OOL + FS7 gas sensor

Measured medium: Gas Flow

Operating temperature range: -40 °C to +85 °C (module)

Flow range: 0 m/s to 50 m/s

Connection type: PCB connector

Supply voltage: 5V DC +/-5%

Output signal: 0 V to 10 V analog

Housing: 45 x 25 mm

Product Old code: 160.00023

Product code: 104018

Product details

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

1-5	CHF 125.00
-----	------------

Sklad: **5**