

Thermal gas flow sensor FS2



Flow range from 0 to 1 m/s (half bridge mode), -20 °C to +150 °C, detection of flow direction

The Thermal gas flow sensor FS2 boasts excellent long-term stability and reproduceability. It detects flow direction and measures a flow range from 0 to 1 m/s (half bridge mode) and operates between -20 °C to +150 °C.

Product Name: FS2T.0.1E.025

Medium: Gas Flow

Strömungsrichtung: Two directions (kalorimetric)

Betriebstemperaturbereich: -20 °C to +150 °C

Chipgrösse/Abmessungen: 5.0 x 3.5 x 0.2 mm

Anschluss: Enamelled copper wire

Drahtlänge: Ø 0.2 mm, 25 mm long

Messbereich (full bridge mode): 0 m/s to 1 m/s resp. 0 ml/min to 50 ml/min

Flow range CTA mode: 0/ms to 100 m/s resp. 0 l/min to 5 l/m

Ansprechzeit T63: < 0.5 s

Sensitivität: 0.001 m/s (50 µL/min)

Substrat: Ceramic

Product Old code: 050.00130

Product code: 103663

Product details

Product description FS2

The IST AG FS2 flow sensors are optimal for measuring gas flow and direction. The IST AG FS2 flow sensors are applicable in gas and offer excellent long-term stability. In addition to measuring flow rates, the FS2 gas flow sensor is able to detect flow direction with outstanding sensitivity. The FS2 is made of ceramic and glass which are inert, even if used in direct contact with 100% oxygen.

Benefits & Characteristics of the FS2

- Simple signal processing
- Simple calibration
- Bare sensor resists up to +450 °C (customer specific)
- Stable platinum technology
- Excellent reproducibility
- No moving mechanical parts

[Customer-specific sensor available upon request](#)

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

5-49	CHF 26.34
------	-----------

50-99	CHF 20.91
-------	-----------

100-150	CHF 18.50
---------	-----------

Lager: **109**