



innovative
Sensor
Technology

Infrared-Emitter HIS2000R-0WC



Thermal infrared emitter with gold plated reflector and Winston cone collimator

HIS2000R-0WC is a NiCr filament based thermal emitter in a TO8 package, with a gold plated reflector as well as a gold plated Winston cone collimator. While the reflector directs the radiation emitted from the rear of the filament to the front, the Winston cone collimator bundles and focuses the beam for maximum optical performance. The open emitter offers high power for a wide spectral measuring range.

Product Name: HIS2000R-0

Gehäuse: TO-8

Strahlungselementbereich: 40 mm²

Strahlungsemission: > 0.9

Strahlungstemperatur: 630 °C at 2.5 W

Optische Ausgangsleistung: up to 830 mW

Max. elektrische Leistung (DC): 2.5 W

Max. elektrische Spannung: 3.8 V

Max. elektrischer Strom: 660 mA

Elektrischer Widerstand: 5...6 Ω

Modulationsfrequenz: 4 Hz
Filter/Fenster: None
Wellenlängenbereich: 2 to 20 μm
Füllgas: None
Product code: 154103

Product details

HISpower series

High-power infrared sources in TO-8 housing

HISpower series emitters have an integrated gold-plated reflector that directs the radiation emitted from the rear filament side to the front through the housing window in order to achieve maximum efficiency and optical output power. All our emitters offer minimum drift at a constant electrical resistance. Infrasolid's infrared emitters are characterized by a very low temperature coefficient of electrical resistance. Therefore, the hot resistance and the cold resistance are almost identical which eases the electrical control of the IR sources. Infrasolid's advanced packaging technology SOLIDSEAL® allows soldered sapphire, CaF_2 and BaF_2 windows for use in a wide temperature range of -25 °C up to +85 °C.

Key features HISpower series

- Pulsable thermal infrared source mounted in an industry standard TO-8 package
- Patented nanostructured radiating element generates black-body spectrum
- Wide wavelength range enables a broad range of applications
- Highest optical output power of up to 1 W
- Soldered, high-quality filter windows guarantee long-term stable operation and high lifetime

INFRASOLID® nanostructure technology

Infrasolid's patented nanostructure technology allows the fabrication of extremely thin and very heat-resistant black optical coatings. They are already used in our thermal infrared light sources but also in optical detector technologies and for stray light absorption in optical measurement systems. The broad spectral range of high

absorption extends from UV up to far infrared wavelengths. A structuring of the black coatings can be done by photolithography to realize very small structures or local areas of blackening. The deposition is done on flat substrates. Temperature-sensitive materials, such as plastics, can be coated using our low temperature black coating process.

Infrared-Emitter HIS2000R-OWC > Details

The online shop

Quantity (pieces)	Price (per piece)
--------------------------	--------------------------

1-4	CHF 116.48
-----	------------

5-9	CHF 105.28
-----	------------

10-24	CHF 99.68
-------	-----------

Lager: **2**