




innovative
Sensor
Technology

Kraftsensor zentriert KZ-011-0400- 18N-E0-K1-G0



Kraftbereich: 18 N - Krafteinleitung: Ohne (nur Loch) - Kontaktierung: Einzellitzen (20cm) mit PicoBlade Stecker - Gehäuse: Ohne Gehäuse

Bei diesem kompakten Kraftsensor wird die Kraft auf einen Rundkopfniet in der Mitte eingeleitet. Der Sensor kann sehr einfach in einem Sackloch mit einem Durchmesser von 12 mm (0,472 in) und einem Spiel montiert werden. Durch die flexiblen Kontaktierungs- und Gehäuseoptionen eignet sich dieser Sensor für vielfältige

Anwendungen.

Product Name: KZ-011-0400-18N-E0-K1-G0

Force range: 18 N

Application of force: None (hole only)

Electrical contacting: Stranded wires (20cm) with PicoBlade connector

Housing: None

Allowable overload: 27 N

Sensitivity: 158 $\mu\text{V/V/N}$

Supply voltage: 0...15 V DC

Supply current: 1.5 2.5 mA at 10 V supply voltage

Output signal span: 0 3.0 mV/V

Bridge resistance: 4.0 6.0 k Ω

Zero offset: -0.1 0.1 mV/V

Zero repeatability: ± 0.02 %FS

Sensitivity tolerance: ± 10 %

Sensitivity repeatability: ± 0.3 %

Linearity error: ± 0.2 %FS

Thermal shift for zero: ± 0.02 %FS/ $^{\circ}\text{C}$

Thermal shift for sensitivity: 0.02 0.03 %/ $^{\circ}\text{C}$

Substrate material: Stainless Steel 1.4542 / X5CrNiCuNb16-4 /17-4 PH $^{\circ}$

Modulus of elasticity: $197 \cdot 10^3$ MPa ($28.5 \cdot 10^{-6}$ ksi)

Substrate thickness: 0.5 mm

Dimensions (LxWxH): 10.5 x 9.0 x 1.1 mm

Operating temperature range: -20 125 $^{\circ}\text{C}$

Ambient humidity: 0 95 %RH non-condensing

Ingress protection: IP44

Packaging: Plastic bag and label with individual calibration data

Product code: 155882

Product details

Centered Force Sensors Nesthorn KZ-011-400

The centered force sensor Nesthorn KZ-011-0400 can be inserted into a blind hole with a diameter of 12 mm. The force application point is right in the middle. Due to the many available force ranges between 18 and 300 N, the possibility of applying force on both sides and the three contact variants, the sensor is suitable for a wide range of

applications. It can be used, for example, in medical devices, measuring and testing devices or industrial plants. Versions with a laser-welded metal housing are also available for particularly easy installation and mechanical protection.

[> View data sheet Nesthorn KZ-011-0400](#)

[> Download brochure](#)

Outstanding sensor properties thanks to thin-film technology

Senstech force sensors are manufactured using thin-film technology. This makes them particularly reliable and long-term stable because the measuring element is applied directly to the metal using sputtering technology. Unlike bonded strain gauges, there are no adhesives and no creeping layers which reflects in the typical technical properties:

- Best long-term stability with drift < 0.03%/year
- High temperature stability even without temperature compensation (typically < 0.01%/°C)
- Very good linearity with correctly designed measuring bodies
- Excellent miniaturization possibilities
- Simple signal processing

Senstech is a pioneer in thin-film based sensor technology. The broad knowledge and experience flows into all of their products.

The perfect fit for your application

Thanks to Senstech's flexible manufacturing processes, it quickly pays off to adapt a sensor to your individual requirements. All essential parameters can be customized:

- Geometry and material of the sensor
- Layout of the thin film elements
- Mechanical and electrical interfaces
- Signal processing

The first prototypes can usually be delivered within a few weeks. Didn't find the right sensor in the webshop? Contact Senstech for an individual offer

[Contact your specialist for force sensors \(senstech.ch\)](https://www.senstech.ch)

Kraftsensor zentriert KZ-011-0400-18N-E0-K1-G0 > Details

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

1-9	CHF 82.50
-----	-----------

10-19	CHF 62.50
-------	-----------

20-50	CHF 47.50
-------	-----------

Lager: **37**