




innovative  
Sensor  
Technology

# Analoger Temperatursensor IC T092



Analog Temperature Sensor Tsic -50°C to 150°C

The TSic 306/303/301 Series of temperature sensor ICs is specifically designed as a low-power solution for temperature measurement in building automation, industrial and mobile applications.

**Product Name:** Tsic 301 T092

**Accuracy:**  $\pm 0.3^{\circ}\text{C}$  im Bereich von  $+10^{\circ}\text{C}$  bis  $+90^{\circ}\text{C}$

**Output signal:** Analog (output 0 to 1 V DC)

**Package/housing:** TO-92

**Supply voltage:** 5V

**Product code:** 103492

## Product details

**TSic 306/303/301 - Accuracy of  $\pm 0.3$  K in a range of 80 K**

The characteristics of the TSic 306/303/301 sensors at a glance:

- Fully calibrated
- Custom calibration and assembly available
- Outstanding accuracy of  $\pm 0.3$  K (TSic 30x)
- Calibrated accuracy range of 80 K can be shifted (default: +10 °C to +90 °C)
- Very low power consumption
- Available with digital, analog and ratiometric output signal

The TSic 306/303/301 Series of temperature sensor ICs is specifically designed as a low-power solution for temperature measurement in building automation, industrial and mobile applications. With a standard calibration and an accuracy of  $\pm 0.3$  K in a temperature range of 80 K (e.g. +10 °C to +90 °C), the TSic sensors are more accurate than a class F0.3 (IEC 60751) platinum sensor in the range of 80 K. The range can be shifted up or downwards to reach a high accuracy of between e.g. -30 °C to +50 °C.

The TSic has a high precision bandgap reference with a PTAT (proportional-to-absolute-temperature) output, a low-power and high-precision ADC and an on-chip DSP core with an EEPROM for the precisely calibrated output signal. The TSic temperature sensor is fully calibrated, meaning no further calibration effort is required by the customer. Extended long wires (> 10 m) will not influence the accuracy.

The TSic 306/303/301 sensors are available with digital (ZacWire, TSic x06), analog (0 V to 1 V, TSic x01) or ratiometric (10 % to 90 % V+, TSic x03) output signal. The low power consumption makes it suitable for many applications.

## Qualität

Entsprechend den bekannten hohen Qualitätsstandards in der Schweiz ist die IST AG nach ISO 9001:2015 (Qualität) und ISO 14001:2015 (Umwelt) zertifiziert.

Entsprechende Prozesse sind Teil unserer täglichen Arbeit. Sie werden regelmässig überprüft und parallel zum Wachstum unseres Unternehmens erweitert.

[> Mehr dazu](#)

## The online shop

**Quantity (pieces) Price (per piece)**

10-49

CHF 8.61

**Quantity (pieces) Price (per piece)**

50-99 CHF 6.84

100-150 CHF 6.05

Lager: **251**