

Humidity module for meteorological applications



RH/T module factory-calibrated for high altitude / low temperature measurement

Digital (I2C) module for relative humidity and temperature designed for excellent reproducibility and response time required in meteorological balloons and drones. Extra fast measurement. Suitable for operation measurement down to -80 °C.

Product Name: HYT.R411

Betriebsfeuchtebereich: 0 % RH to 100 % RH

Betriebstemperaturbereich: -80 °C to +50 °C

Genauigkeit Feuchte: ± 2 % RH at 23 °C (0 % RH to 90 % RH)

Genauigkeit Temperatur: ± 0.2 K (0 °C to +50 °C); ± 0.5 K (-80 °C to 0 °C)

Digitale Schnittstelle: I²C

Betriebsspannung: 2.1 V to 3.6 V

Stromverbrauch: < 80 μ A at 10 Hz measuring rate

Abmessungen: 19.6 x 6.1 x 2.0 mm

Anschlüsse: SIL RM

Drahtlänge: 8 x 0.5 mm

Medium: Air/Gas

Product code: 153690

Product details

Humidity module for meteorological applications > Details

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

1-9	CHF 103.00
-----	------------

10-20	CHF 82.40
-------	-----------

Lager: **31**