

Thermal gas flow sensor FS7



Flow range from 0 to 100 m/s, -20 °C to +150 °C

For measuring flow rates using a symmetrical heater design and having an excellent sensitivity and reproducibility. This all-rounder features long-term stability and reproducibility.

Product Name: FS7.0.1L.195

Medium: Gas Flow

Strömungsrichtung: One direction (anemometric)

Betriebstemperaturbereich: -20 °C to +150 °C

Chipgrösse/Abmessungen: 6.9 x 2.4 x 0.20 mm

Anschluss: Cu/Ag stranded wire, PTFE-insulated

Drahtlänge: 195 mm

Flow range CTA mode: 0/ms to 100 m/s

Ansprechzeit T63: ~200 ms (jump from 0 to 10000 sccm)

Sensitivität: 0.01 m/s

Substrat: Ceramic

Draht: 3 pins, Cu/Ag-stranded wires, PTFE insulated

Product Old code: 050.00216

Product code: 103705

Product details

Product description FS7

The IST AG FS7 thermal mass flow sensors are the successors of the FS5 flow sensors and exhibit a symmetrical heater design and enhanced sensitivity. The FS7 flow sensor is applicable in gas and offer excellent long-term stability. The small thermal mass of the FS7 sensor provides a fast response time. Additionally, the standard FS7 sensor is also available with a housing which is easily implemented into various applications.

The IST AG FS7 flow sensors are optimal for measuring gas flow in various flow applications.

Benefits & Characteristics of the FS7 gas flow sensor

- Easy adaptation in various applications and housings
- Excellent long-term stability
- Simple signal processing
- Simple calibration
- Stable platinum technology
- Excellent reproducibility

[Customer-specific sensor available upon request.](#)

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

5-49	CHF 27.76
------	-----------

50-99	CHF 22.04
-------	-----------

100-150	CHF 19.50
---------	-----------

Lager: **109**