



innovative  
Sensor  
Technology

## FS7 EvaKit



Flow Demo Board with FS7 Sensor: evaluation electronics for anemometric (thermal) flow sensors

Ideal for testing FS7 sensors in your application.

**Product Name:** Flow Eval Board FS/OOL + FS7 gas sensor

**Measured medium:** Gas Flow

**Operating temperature range:** -40 °C to +85 °C (module)

**Flow range:** 0 m/s to 50 m/s

**Connection type:** PCB connector

**Supply voltage:** 5V DC +/-5%

**Output signal:** 0 V to 10 V analog

**Housing:** 45 x 25 mm

**Product Old code:** 160.00023

**Product code:** 104018

# Product details

## FS7 EvaKit > Details

### The online shop

| Quantity (pieces) | Price (per piece) |
|-------------------|-------------------|
|-------------------|-------------------|

|     |            |
|-----|------------|
| 1-5 | CHF 128.75 |
|-----|------------|

Stock: **4**