

# Capacitive Humidity Sensor P14 Rapid-2 (650pF +/-150 pF)



Ultra- fast response time. Optimal for weather balloons and radiosondes, -80 °C to +150 °C, 5.0 x 3.81 mm, 10 mm wires

Capacitive humidity sensor P14-Rapid-2 with wires. Stable and robust humidity sensor with extraordinarily fast response time, optimal for meteorology applications.

**Product Name:** P14 Rapid-2 (650pF +/-150 pF)

**Capacitance:** 650pF +/-150pF (at +23 °C and 30 % RH)

**Operating humidity range:** 0 % RH to 100 % RH

**Operating temperature range:** -80 °C to +150 °C

**Dimensions:** 5.0 x 3.81 x 0.4 mm

**Connection type:** Au/Cu Wire

**Wire dimensions:** Ø 0.4 mm, 10 mm long

**Response time:** 0.3s

**Measured medium:** Air/Gas

**Product code:** 104932

# Product details

## P14 Rapid - Optimal for weather balloons and radio sondes

Stable and robust humidity sensors with ultra-fast response time are often required in applications involving meteorology – not only in normal conditions, but also under elevated environmental constraints such as extremely low temperatures, high radiation levels and under extreme condensation. Such applications need fully tailored solutions, such as those provided by the Innovative Sensor Technology IST AG P14 Rapid. The P14 Rapid humidity sensor combines speed and full range operation in an ideal way. The sensor is capable of measuring 0 % RH to 100 % RH (maximal dew point +85 °C) with a capacitance of 140 pF  $\pm$ 40 pF (wired) / 180 pF  $\pm$ 50 pF (SMD) (at 30 % RH and +23 °C) and operates within a temperature range of -80 °C to +150 °C.

## Benefits & Characteristics of this humidity sensor

- High chemical resistance
- Very low drift
- Wide temperature range
- High humidity stability
- Resistance to condensation
- Fast recovery time

[Customer-specific sensor available upon request](#)

## Alternative wires

The IST AG P14-W humidity sensor is available with CuP-SIL-wire post-plated with Sn, Au/Cu-wire or as SMD for automatic packaging as standard.

## Quality

Consistent with the well-known, high-quality standards in Switzerland, IST AG is certified according to ISO 9001:2015 (quality) and ISO 14001:2015 (environment). Appropriate processes are part of our daily work. They are regularly audited and

extended parallel to the growth of our company.

[> Read more](#)

## The online shop

Quantity (pieces)	Price (per piece)
1-10	CHF 35.60
11-50	CHF 28.25
51-100	CHF 25.00

Stock: **178**