


## BondSens Pt1000 class F0.3



Bondable platinum 1000 Ohm RTD component, temperature range -50° C to 150° C, chip tray (sensor side up)

IST AG's smallest temperature sensor with 0.1 x 0.2 mm (LxW) bondable contacts

**Product Name:** P1K0.0707.3FC.B.T.S

**Nominal resistance:** 1000  $\Omega$  at 0 °C

**Operating temperature range:** -50 °C to +150 °C

**TCR:** Pt 3850 ppm/K

**Chip size/dimensions:** 0.75 x 0.75 x 0.3 mm

**Tolerance/class:** IEC 60751 F0.3 (IST AG tolerance class B)

**Connection type:** Bondable pads (Au)

**Packaging:** Chip tray, sensor-side up

**Product code:** 104316

### Product details

## **BondSens (0.75 x 0.75 mm)**

IST AG's smallest platinum temperature sensor operates within a temperature range of -50 °C to 150 °C (according to DIN EN 60751) and is designed for automatic placement in high volume applications on printed circuit boards where long term stability, interchangeability, combined with low cost are important. This RTD is typically used in energy management for thermal compensation, industrial and medical devices.

It features a very small size of 0.75mm x 0.75mm with very low drift and can be integrated within semiconductor devices. It is also designed for Au-wire bonding.

Customized adaptations are available on request

## **Platinum Sensors**

Innovative Sensor Technology IST AG platinum temperature sensors provide solutions for extreme temperature applications and are designed with the highest quality materials, allowing them to operate within a wide temperature range of -200 °C to +1000 °C. Standard IEC 60751 sensors are offered in class F0.3 (0.12 %), class F0.15 (0.06 %), F0.1 (0.04 %), and higher accuracies upon request. Our sensors are available in wireless (SMD) and wired configurations, and in sizes ranging from 0.75 mm to 10 mm (L), and 0.75 mm to 5.08 mm (W). Standard sensors can be customized with a variety of lead wire material, insulations, length, and configurations.

With many years of experience, IST AG also offers development of customer-specific applications in terms of sensor technology development and consultation. As part of the standard development process, IST AG offers support at the point of implementation - this way we ensure the best sensor solution for specific applications.

[More information on platinum temperature sensors](#)

## **Small dimensions**

IST AG offers various sensor solutions for applications with limited space requirements.

## **MiniSens**

The IST AG MiniSens offers the smallest footprint with dimensions of only 1.2 mm x 1.6 mm making the sensor an optimal solution for limited space applications. The MiniSens is available with accuracies of up to IEC 60751 F0.1 (IST AG reference class Y) and with long directly welded wires. The sensor can be used in applications with an operation temperature range of up to +600 °C.

The MiniSens is also offered with a metallized backside enabling optimal thermal coupling.

## **SlimSens**

The IST AG SlimSens sensor is specially developed for applications requiring sensors fitted into tubes with very small diameters. The SlimSens measures 0.8 mm x 3 mm and is the optimal solution for applications with tube diameters from 1 mm. The SlimSens is available with accuracies of up to IEC 60751 F0.1 (IST AG reference class Y) and with long directly welded wires within various ohmic resistances. This Pt temperature sensor can be used in applications with an operation temperature range of up to +600 °C.

## **SMD and FlipChip**

### **SMD**

IST AG offers wireless RTD Platinum SMD sensors for automatic PCB assembly processes with wrap-around contacts on both ends. We offer different SMD technologies for different applications and temperature ranges, e.g. SAC305-tinned wrap-around contacts for the normal PCB assembly process, high temperature solder wrap-around contacts for high temperature applications up to +250 °C or Ni/Au wrap-around contacts for special requirements or wire bonding applications. The SMD sensors are available with various accuracies of up to IEC 60751 F0.15 (IST AG reference class A) and in different dimensions (0805/1206) with other dimensions upon request. SMD sensors are characterized by excellent long-term stability, fast response time and low self-heating.

The wireless IST AG FlipChip series features Pt temperature sensors with excellent long-term stability, fast response time and low self-heating. The FlipChips are developed with contacts on one side resulting in no short-cut risk on the backside of the chip. Furthermore, IST AG offers different FC technologies for different assembly processes (reflow-soldering, bonding or welding). The FC sensors are available with accuracies of up to IEC 60751 F0.3 (IST AG reference class B) and in different dimensions (0603/0805/1206/further dimensions on request) with other

dimensions available on request.

## FlipChip

The FC sensors are optimal for applications with limited space requirements and offer an optimal price/performance ratio. Due to the small mechanical dimensions, a standard 0805 FC will use the same space as a standard 0603 SMD sensor on a PCB.


## Quality

Consistent with the well-known, high-quality standards in Switzerland, IST AG is certified according to ISO 9001:2015 (quality) and ISO 14001:2015 (environment). Appropriate processes are part of our daily work. They are regularly audited and extended parallel to the growth of our company.

[> Read more](#)

## The online shop

Quantity (pieces)	Price (per piece)
100-249	CHF 5.50
250-499	CHF 4.75
500-2500	CHF 3.95

 **1724**