



# DigiPicco™ Basic I<sup>2</sup>C


## Capacitive Humidity Module

### With calibrated and linearized I<sup>2</sup>C output signal

#### Benefits & Characteristics

- Precise humidity and temperature measurement
- Fully calibrated
- Very low drift due to wide sensor area
- Excellent response time
- Integrated Pt1000 temperature sensor and P14 humidity sensor
- Module with external sensor available
- Calibrated humidity and temperature signals on one bus
- PCB moisture protected
- Customer-specific module available upon request

#### Illustration<sup>1)</sup>



1) For actual size, see dimensions

#### Technical Data

Dimensions (L x W x H / H2 in mm):	47 x 10 x 1 / 2.8		
Operating humidity range:	0 % RH to 100 % RH (maximal dew point = +85 °C)		
Operating temperature range:	Module:	With external sensor:	
	P14:	MK33:	
	-25 °C to +85 °C	-50 °C to +150 °C	-40 °C to +190 °C
Humidity sensor:*	P14 SMD		
Temperature sensor:*	Pt1000, class B (IEC 60751 F0.3)		
Humidity accuracy:	< ±3 % RH (15 % RH to 85 % RH at +23 °C)		
	< ±5 % RH (0 % RH to 15 % RH and > 85 % RH at +23 °C)		
Temperature accuracy:	±0.5 K (-25 °C to +85 °C)		
Response time $t_{63}$ :	< 5 s (50 % RH to 0 % RH) at +23 °C		
Operating voltage ( $V_{CC}$ ):	5 $V_{DC}$		
Current consumption:	< 3 mA		




Output signal:	0x0 to 0x7FFF (0 % RH to 100 % RH) 0x0 to 0x7FFF (-40 °C to +125 °C)
Cycle rate:	59 Hz
I <sup>2</sup> C standard address:*	0x78
Connection:*	Soldering pads for V <sub>CC</sub> , clock and data (I <sup>2</sup> C), GND
Storage conditions:	-40 °C to +80 °C at max. 95 % RH non condensing
Cable (external sensor version only):	PTFE, 1 m (other lengths on request)

\* Customer-specific alternatives available

### Pin Assignment

W1	W2	W3	W4	W5	W6	W7	W8	W9	W10
		Clock SCL (I <sup>2</sup> C)	Data SDA (I <sup>2</sup> C)				GND		V <sub>CC</sub> +



### Order Information - Module

	DigiPicco (TM) Basic I2C-G
Order code	150.00015

### Order Information - Module with PTFE cable, 1 m

	DigiPicco (TM) Basic I2C-G.S
Order code	150.00092

### Additional Documents

Application Note:	Document name: AHLin_Digi_E
-------------------	--------------------------------



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland  
 Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved