







The calibration of the sensor must be done 5 days after soldering at the earliest.

## Characteristic Curve

### Wired



### SMD





Order Information - SIL (CuP-SIL-wire post-plated with Sn, 10 mm)

Order code	P14 (150pF ±50pF) 040.00191
------------	--------------------------------



Order Information - SMD

Order code	P14 SMD-G (180pF ±50pF) 040.00109
------------	--------------------------------------



Order Information - Au/Cu-wire, Ø 0.4 mm, 10 mm

Order code	P14-W (150pF ±50pF) 040.00174
------------	----------------------------------

Order Information - Cu/Ag-wire, 18 mm, AWG26, PTFE, insulated 8 mm

Order code	P14.S-W (150pF ±50pF) 040.00184
------------	------------------------------------

