



B.CPP1.800

Circular Peristaltic Pump


For high pump rates in fluids and gases

A product of Jobst Technologies

Benefits & Characteristics

- Pumping of various liquids and gases
- Pump rates in the range 70 μl – 800 $\mu\text{l}/\text{min}$
- Medium only in contact with medical grade silicone tube
- Small footprint
- Evaluation kit available that allows to control up to 4 pumps via plug & play to the USB port of a computer

Illustration




Technical Data


Dimensions (L x W x H in mm):	8.4 x 10.7 x 31.4
Weight:	3.3 g (without connector)
Flow range:	70 μl to 800 $\mu\text{l}/\text{min}$
Operation:	Bi-directional
Outlet pressure:	Up to 2 bar overpressure
Self-priming:	< -0.9 bar
Typical current:	30 mA at 3.3V
Max. voltage:	$\pm 3.3\text{V DC}$
Tube material:	Silicone (ISO 10993-1, USP class 1-6)
Tube dimension:	0.5 mm (inner \varnothing) / 1.3 mm (outer \varnothing)
Lifetime typical:	>50 operating hours at 3V >340 operating hours at 1.5V
Available connectors:	JST-SH female, pin-head male or pin-head female



Pump Rate



Product Image





Order Information

	Connector	Wire length*
Order code	JST-SH female MP.CPP1.800.DWBP.33.JSF.168.SI01	168 mm
Order code	Pin-head male MP.CPP1.800.DWBP.33.PHM.018.SI01	18 mm
Order code	Pin-head female MP.CPP1.800.DWBP.33.PHF.018.SI01	18 mm

* different wire lengths upon request

Disclaimer

Not for medical, diagnostics and usage on humans. For evaluation use only.



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved