



SFS01 (Silicon Flow Sensor)

Thermal mass flow sensor

Optimal for fast measuring of gas flow and direction

Characteristics & Applications


Characteristics:

- Measurement from 0.0 to 3.5 m/s (Gas)
- Detection of flow direction
- Very fast response time
- Very low power requirement
- Easy system integration

Applications:

- Automation technology
- Process and regulation technology
- Medicinal and biological technology
- Air conditioning
- Battery-operated applications in portable devices

Illustration



1) For exact size see measurements



Technical Sensor Data

Measurements (L x B x H in mm):	6.00 (±0.05) x 2.00 (± 0.02) x 0.525 (±0.01)
Temperature range:	0 °C to +80 °C
Storage temperature:	-20 °C to +80 °C
Compressive load:	up to 1 bar (one-sided on membrane for a duration of 10 years)

Electrical Sensor Data

Connection:	Bond pads (recommended bonding process: wedge-wedge with aluminum wires)
Heater resistance:	1'000 Ω ± 20 %
Thermopile resistance:	< 40 kΩ
Thermopile sensitivity:	> 5 mV/mW
Thermopile synchronization sensitivity:	< 9 %
Thermopile voltage:	typically 5.5 mV/K
Heater output:	typically 3-10 mW (air), maximum tolerance: 20 mW

Flow Performance

The following values are viewed as typical and achieved in laboratory conditions. The gas used was nitrogen.


Medium:	non-aggressive gases (5-95 % rel. humidity, non-condensating)
Measurement range:	0.0 to 3.5 m/s
Sensitivity:	0.002 m/s*
Response time t_{63} :	5 ms
Accuracy:	0.2 % F.S.**
Temperature sensitivity (uncomp.):	< 0.18 %/K F.S.*
Sensitivity to positioning:	< 0.1 % F.S.
Humidity sensitivity:	< 4.0 % F.S.

* dependent on electronics

** dependent on calibration



Bondpad-configuration



1	2	3	4	5	6
n.c.	TP1+ Thermopile 1 (hot end)	TP1- Thermopile 1 (cold end)	n.c.	n.c.	Hz1 - left heater (heater series connection supply voltage)
7	8	9	10	11	12
Hz2 - right heater (heater series connection supply voltage)	n.c.	n.c.	TP2- Thermopile 2 (cold end)	TP2+ Thermopile 2 (hot end)	Hzcom heater at parallel circuit/mutual connection

Order Information

Sensor element	SFS01
Order code	105050
Former order code	350.00312

Additional Electronics

EvaKit	SFS01 EvaKit
Order code	105059
Former order code	350.00330



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved