



MK33-W


Capacitive Humidity Sensor

Optimal for oil measurement applications

Benefits & Characteristics

- High chemical resistance
- Wide temperature range
- Condensation resistant
- Fast recovery time
- Very low drift
- High humidity stability
- Suitable for extreme environments
- Customer-specific sensor available upon request

Illustration¹⁾



1) For actual size, see dimensions

Technical Data


Dimensions (L x W x H / H2 in mm):	SIL	10.8 x 3.81 x 0.4 / 1.2
	Au/Cu-wire	10.8 x 3.81 x 0.4 / 0.8
Operating humidity range:	0 % RH to 100 % RH (maximal dew point +95 °C)	
Operating temperature range:	-40 °C to +190 °C	
Capacitance (C ₃₀):*	300 pF ±40 pF (at 30 % RH and +23 °C)	
Sensitivity (at C ₃₀ = 300 pF):	0.45 pF/% RH (15 % RH to 90 % RH)	
Loss factor:	< 0.01 (at 23 °C, at 10 kHz, at 90 % RH)	
Linearity error:	< 2 % RH (15 % RH to 90 % RH at +23 °C after one point calibration)	
Hysteresis:	< 2 % RH	
Response time t ₆₃ :	< 6 s (50 % RH to 0 % RH at +23 °C)	
Temperature dependence (typical):	$\Delta \% RH = (B1 \times \% RH + B2) \times T [^\circ C] + (B3 \times \% RH + B4)$ B1 = 0.0011 [1/°C] B2 = 0.0892 [% RH/°C] B3 = -0.0268 B4 = -2.079 [% RH]	
Measurement frequency:	1 kHz to 100 kHz (recommended 10 kHz)	
Maximal supply voltage:	< 12 V _{pp} AC	
Signal form:	alternating signal without DC bias	
Connection:*	CuP-SIL-wire post-plated with Sn, 10 mm or Au/Cu-wire, Ø 0.4 mm, 10 mm or Au/Cu-wire, Ø 0.4 mm, 12 mm, PTFE insulated, solder joints and pads covered with silicone globtop	

* Customer-specific alternatives available




The calibration of the sensor must be done 5 days after soldering at the earliest.

Characteristics Curve



Product photo





Order Information - SIL (CuP-SIL-wire post-plated with Sn, 10 mm)

	MK33 (300pF ±40pF)
Order code	103581
Former order code	040.00192

Order Information - Au/Cu-wire, Ø 0.4 mm, 10 mm

	MK33-W (300pF ±40pF)
Order code	103575
Former order code	040.00180

Order Information - Au/Cu-wire, Ø 0.4 mm, 12 mm PTFE insulated, solder joints and pads covered with silicone globtop

	MK33-W HMN300-40.1138.W.012.S
Order Code	151306



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved