



P14-W

Capacitive Humidity Sensor

Optimal for various humidity applications

Benefits & Characteristics

- High chemical resistance
- Wide temperature range
- Resistance to condensation
- Fast recovery time
- Very low drift
- High humidity stability
- Customer-specific sensor available upon request

Illustration¹⁾



1) For actual size, see dimensions

Technical Data

	Wired	SMD
Dimensions (L x W x H / H2 in mm):	5 x 3.81 x 0.4 / 0.8	6.35 x 2.54 x 0.4
Capacitance at 30 % RH and +23 °C (C_{30}):*	150 pF ±50 pF	180 pF ±50 pF
Sensitivity at C_{30} = 150 pF/ 180 pF (15 % RH to 90 % RH):	0.25 pF/% RH	0.3 pF/% RH
Operating humidity range:	0 % RH to 100 % RH (maximal dew point +85 °C)	
Operating temperature range:	-50 °C to +150 °C	
Loss factor:	< 0.01 (at +23 °C, at 10 kHz, at 90 % RH)	
Linearity error:	< 1.5 % RH (15 % RH to 90 % RH at +23 °C after one point calibration)	
Hysteresis:	< 1.5 % RH	
Response time t_{63} :	< 5 s (50 % RH to 0 % RH at +23 °C)	
Temperature dependence (nominal):	$\Delta \% RH = (B1 \times \% RH + B2) \times T [^\circ C] + (B3 \times \% RH + B4)$ $B1 = 0.0014 [1/^\circ C]$ $B2 = 0.1325 [\% RH/^\circ C]$ $B3 = -0.0317$ $B4 = -3.0876 [\% RH]$	
Measurement frequency:	1 kHz to 100 kHz (recommended 10 kHz)	
Maximal supply voltage:	< 12 V_{pp} AC	
Signal form:	alternating signal without DC bias	
Connections:*	CuP-SIL-wire post-plated with Sn, 10 mm or Au/Cu-wire, Ø 0.4 mm, 10 mm, or SMD, automatic assembly compatible	


* Customer-specific alternatives available




The calibration of the sensor must be done 5 days after soldering at the earliest.

Characteristic Curve

Wired





SMD





Product Photos



Order Information - SIL (CuP-SIL-wire post-plated with Sn, 10 mm)

	P14 (150pF ±50pF)	
Order code	103580	replaced by 150473
Former order code	040.00191	

Order Information - SMD

	P14 SMD-G (180pF ±50pF)	
Order code	103562	
Former order code	040.00109	

Order Information - Au/Cu-wire, Ø 0.4 mm, 10 mm

	P14-W (150pF ±50pF)	
Order code	103572	replaced by 150466
Former order code	040.00174	

Order Information - Cu/Ag-wire, 18 mm, AWG26, PTFE, insulated 8 mm

	P14.S-W (150pF ±50pF)	
Order code	103577	replaced by 150470
Former order code	040.00184	



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved