



## 600 °C Series



### Platinum temperature sensor with wires

For high temperatures




#### Benefits & characteristics

- Excellent long-term stability
- Low self-heating
- Fast response time
- Small dimensions
- Vibration and temperature shock resistant
- Paired sensors available
- 1/5 IEC and 1/10 IEC available
- Customer-specific sensor available upon request



#### Illustration <sup>1)</sup>



H = Substrate Hight

H2 =Hight

W = Width

L = Length

L<sub>w</sub> = Wire length

Dimension tolerances:

W ±0.2 mm, L ±0.2 mm, H ±0.1 mm, H2 ±0.3 mm,  
L<sub>w</sub> (up to 30 mm) ±1 mm

<sup>1)</sup> for actual size see dimensions in order information



## Technical Data



Operating temperature range: -200 °C to +600 °C



Nominal resistance:\*

- 100 Ω at 0 °C
- 100 Ω at 0 °C
- 500 Ω at 0 °C
- 1000 Ω at 0 °C
- 2000 Ω at 0 °C



Characteristics curve:\* 3850 ppm/K



Long-term stability: < 0.04 % at 1000 h at maximal operating temperature



Tolerance class: *	iST reference	
(dependent on temperature range)	IEC 60751 F0.15	A
	IEC 60751 F0.3	B
	IEC 60751 F0.6	C
	IEC 60751 F0.1	Y

Connection:\* Pt-clad Ni-wire, Ø 0.2 mm (solderable, weldable, crimpable, brazeable)

Design: <sup>2)</sup> ESD optimized

Alternative wire construction:\* Inverted wired

Recommended applied current:<sup>3)</sup>

- 1 mA at 100 Ω
- 0.6 mA at 200 Ω
- 0.5 mA at 500 Ω
- 0.3 mA at 1000 Ω
- 0.2 mA at 2000 Ω

<sup>3)</sup> Self-heating must be considered

Other alternatives: \*

- Housed in round ceramics (for dry environments only) - see data sheet DTP\_Round\_Housing\_E
- Grouped and paired
- Substrate thickness

\* Customer-specific alternatives available



## Order Information



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

### 6W (Pt-cladded Ni-wire, Ø 0.2 mm)

100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	101371	P0K1.161.6W.Y.007	7	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100945	P0K1.161.6W.A.007	7	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100946	P0K1.161.6W.B.007	7	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	155582	P0K1.161.6W.Y.010	10	2) ESD optimized
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	154366	P0K1.161.6W.A.010	10	2) ESD optimized
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	154367	P0K1.161.6W.B.010	10	2) ESD optimized
500 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	100219	P0K5.161.6W.Y.010	10	
500 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100218	P0K5.161.6W.A.010	10	
500 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100217	P0K5.161.6W.B.010	10	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	100247	P1K0.161.6W.Y.010	10	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100246	P1K0.161.6W.A.010	10	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100245	P1K0.161.6W.B.010	10	
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	153442	P0K1.202.6W.Y.007	7	2) ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	153741	P0K1.202.6W.A.007	7	2) ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	153742	P0K1.202.6W.B.007	7	2) ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155716	P0K1.202.6W.B.007.S	7	packaged in blister of 500 pcs
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155762	P0K1.202.6W.Y.010	10	2) ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	155763	P0K1.202.6W.A.010	10	2) ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155764	P0K1.202.6W.B.010	10	2) ESD optimized
500 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	On request	P0K5.202.6W.Y.007	7	
500 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	On request	P0K5.202.6W.A.007	7	
500 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	101108	P0K5.202.6W.B.007	7	
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155770	P1K0.202.6W.Y.007	7	2) ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	154721	P1K0.202.6W.A.007	7	2) ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155771	P1K0.202.6W.B.007	7	2) ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155774	P1K0.202.6W.Y.010	10	2) ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	155773	P1K0.202.6W.A.010	10	2) ESD optimized
1000 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155772	P1K0.202.6W.B.010	10	2) ESD optimized



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	101401	P0K1.216.6W.Y.007	7	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100589	P0K1.216.6W.A.007 P	7	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100599	P0K1.216.6W.B.007	7	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100429	P0K1.216.6W.Y.010	10	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100414	P0K1.216.6W.A.010	10	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100419	P0K1.216.6W.B.010	10	
1000 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	101042	P1K0.216.6W.Y.010	10	
1000 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100588	P1K0.216.6W.A.010	10	
1000 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100552	P1K0.216.6W.B.010	10	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	100545	P1K0.232.6W.Y.007	7	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	100830	P1K0.232.6W.A.007	7	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100546	P1K0.232.6W.B.007	7	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	153765	P1K0.232.6W.Y.010	10	2) ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	153766	P1K0.232.6W.A.010	10	2) ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	153768	P1K0.232.6W.B.010	10	2) ESD optimized
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	101357	P0K1.232.6W.Y.020	20	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	101356	P0K1.232.6W.A.020	20	
100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100875	P0K1.232.6W.B.020	20	
500 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	100223	P0K5.232.6W.Y.010	10	
500 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	100222	P0K5.232.6W.A.010	10	
500 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100221	P0K5.232.6W.B.010	10	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	100545	P1K0.232.6W.Y.007	7	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	100830	P1K0.232.6W.A.007	7	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100546	P1K0.232.6W.B.007	7	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	153765	P1K0.232.6W.Y.010	10	2) ESD optimized
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	153766	P1K0.232.6W.A.010	10	2) ESD optimized
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	153768	P1K0.232.6W.B.010	10	2) ESD optimized
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	On request	P1K0.232.6W.Y.020	20	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.15 (class A)	151322	P1K0.232.6W.A.020	20	
1000 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100550	P1K0.232.6W.B.020	20	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
200 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K2.420.6W.Y.010	10	
200 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P0K2.420.6W.A.010	10	
200 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	104300	P0K2.420.6W.B.010	10	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.420.6W.Y.007	7	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101077	P1K0.420.6W.A.007	7	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101093	P1K0.420.6W.B.007	7	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.420.6W.Y.010	10	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101288	P1K0.420.6W.A.010	10	
1000 Ω	420	4.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101129	P1K0.420.6W.B.010	10	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.516.6W.Y.007	7	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100835	P0K1.516.6W.A.007	7	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100836	P0K1.516.6W.B.007	7	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100148	P0K1.516.6W.Y.010	10	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100147	P0K1.516.6W.A.010	10	
100 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100146	P0K1.516.6W.B.010	10	
500 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100229	P0K5.516.6W.Y.010	10	
500 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100228	P0K5.516.6W.A.010	10	
500 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100227	P0K5.516.6W.B.010	10	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.516.6W.Y.007	7	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100828	P1K0.516.6W.A.007	7	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100829	P1K0.516.6W.B.007	7	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	100270	P1K0.516.6W.Y.010	10	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	100269	P1K0.516.6W.A.010	10	
1000 Ω	516	5.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100268	P1K0.516.6W.B.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100165	P0K1.520.6W.Y.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100163	P0K1.520.6W.A.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100162	P0K1.520.6W.B.010	10	
500 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100235	P0K5.520.6W.Y.010	10	
500 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100234	P0K5.520.6W.A.010	10	
500 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100233	P0K5.520.6W.B.010	10	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
1000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	156115	P1K0.520.6W.Y.010	10	2) ESD optimized
1000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	156116	P1K0.520.6W.A.010	10	2) ESD optimized
1000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	156117	P1K0.520.6W.B.010	10	2) ESD optimized
2000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P2K0.520.6W.Y.010	10	
2000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P2K0.520.6W.A.010	10	
2000 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100322	P2K0.520.6W.B.010	10	
100 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.538.6W.Y.010	10	
100 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.15 (class A)	100785	P0K1.538.6W.A.010	10	
100 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.3 (class B)	100541	P0K1.538.6W.B.010	10	
1000 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.538.6W.Y.010	10	
1000 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.15 (class A)	On request	P1K0.538.6W.A.010	10	
1000 Ω	538	5.0 x 3.8 x 0.65 / 1.3	F0.3 (class B)	100336	P1K0.538.6W.B.010	10	
1000 Ω	505	5.0 x 5.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.505.6W.Y.010	10	
1000 Ω	505	5.0 x 5.0 x 0.65 / 1.3	F0.15 (class A)	On request	P1K0.505.6W.A.010	10	
1000 Ω	505	5.0 x 5.0 x 0.65 / 1.3	F0.3 (class B)	101208	P1K0.505.6W.B.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100202	P0K1.102.6W.Y.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100201	P0K1.102.6W.A.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100200	P0K1.102.6W.B.010	10	
500 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K5.102.6W.Y.010	10	
500 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100238	P0K5.102.6W.A.010	10	
500 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100237	P0K5.102.6W.B.010	10	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.102.6W.Y.007	7	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P1K0.102.6W.A.007	7	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100474	P1K0.102.6W.B.007	7	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100308	P1K0.102.6W.Y.010	10	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100473	P1K0.102.6W.A.010	10	
1000 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100307	P1K0.102.6W.B.010	10	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

### 6W (Pt-cladded Ni-wire, Ø 0.2 mm, bent 90°), inverted wires

100 Ω	232	2.3 x 2 x 1.1	F0.15 (class A)	101143	P0K1.232.6W.A.010.U.S	10	inverted wires
100 Ω	232	2.3 x 2 x 1.1	F0.3 (class B)	100975	P0K1.232.6W.B.010.U.S	10	inverted wires

### PU (TCR = 3750 ppm/K)

100 Ω	232	2.2 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100260	PU1K0.232.6W.B.010	10	
-------	-----	------------------------	----------------	--------	--------------------	----	--

### 6W (Pt-cladded Ni-wire, Ø 0.2 mm), D (substrate thickness, 0.4 mm)

100 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.232.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.15 (class A)	100463	P0K1.232.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.3 (class B)	100462	P0K1.232.6W.B.010.D	10	substrate thickness 4 mm
1000 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.232.6W.Y.010.D.S	10	substrate thickness 4 mm
1000 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.15 (class A)	On request	P0K1.232.6W.A.010.D.S	10	substrate thickness 4 mm
1000 Ω	232	2.3 x 2.0 x 0.4 / 1.05	F0.3 (class B)	154038	P0K1.232.6W.B.010.D.S	10	substrate thickness 4 mm
100 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.516.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.15 (class A)	100334	P0K1.516.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.3 (class B)	100333	P0K1.516.6W.B.010.D	10	substrate thickness 4 mm
1000 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.1 (class Y)	100340	P1K0.516.6W.Y.010.D	10	substrate thickness 4 mm
1000 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.15 (class A)	100442	P1K0.516.6W.A.010.D	10	substrate thickness 4 mm
1000 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.3 (class B)	100339	P1K0.516.6W.B.010.D	10	substrate thickness 4 mm
100 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K1.520.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.15 (class A)	100169	P0K1.520.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.3 (class B)	100167	P0K1.520.6W.B.010.D	10	substrate thickness 4 mm
100 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.1 (class Y)	On request	P0K1.102.6W.Y.010.D	10	substrate thickness 4 mm
100 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.15 (class A)	100855	P0K1.102.6W.A.010.D	10	substrate thickness 4 mm
100 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.3 (class B)	100337	P0K1.102.6W.B.010.D	10	substrate thickness 4 mm
1000 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.1 (class Y)	On request	P1K0.102.6W.Y.010.D	10	substrate thickness 4 mm
1000 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.15 (class A)	100310	P1K0.102.6W.A.010.D	10	substrate thickness 4 mm
1000 Ω	102	10.0 x 2.0 x 0.4 / 1.0	F0.3 (class B)	100309	P1K0.102.6W.B.010.D	10	substrate thickness 4 mm



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

### 6W (Pt-cladded Ni-wire, Ø 0.2 mm), T (substrate thickness, 0.25 mm)

100 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.1 (class Y)	100121	P0K1.232.6W.Y.010.T	10	substrate thickness 0.25 mm
100 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.15 (class A)	100120	P0K1.232.6W.A.010.T	10	substrate thickness 0.25 mm
100 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.3 (class B)	100119	P0K1.232.6W.B.010.T	10	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.1 (class Y)	On request	P1K0.232.6W.Y.007.T	7	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.15 (class A)	101593	P1K0.232.6W.A.007.T	7	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.25 / 0.9	F0.3 (class B)	101586	P1K0.232.6W.B.007.T	7	substrate thickness 0.25 mm

### 7W<sup>3</sup> (Pt-wire, Ø 0.2 mm), D (substrate thickness, 0.4 mm)

200 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.1 (class Y)	On request	P0K2.516.7W.Y.007.D	7	substrate thickness 4 mm
200 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.15 (class A)	150635	P0K2.516.7W.A.007.D	7	substrate thickness 4 mm
200 Ω	516	5.0 x 1.6 x 0.4 / 1.05	F0.3 (class B)	100880	P0K2.516.7W.B.007.D	7	substrate thickness 4 mm

3) Operating temperature range of -200 °C to +600 °C

### 7W<sup>3</sup> (Pt-wire, Ø 0.2 mm, (161) (232) (520) / Ø 0.15 mm (308))

100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	On request	P0K1.161.7W.Y.010	10	substrate thickness 0.25 mm
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100465	P0K1.161.7W.A.010	10	substrate thickness 0.25 mm
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100446	P0K1.161.7W.B.010	10	substrate thickness 0.25 mm
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100895	P0K1.232.7W.Y.010	10	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100511	P0K1.232.7W.A.010	10	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100341	P0K1.232.7W.B.010	10	
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.1 (class Y)	100561	P0K1.308.7W.Y.007	7	substrate thickness 0.25 mm
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.15 (class A)	100537	P0K1.308.7W.A.007	7	substrate thickness 0.25 mm
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.3 (class B)	100538	P0K1.308.7W.B.007	7	substrate thickness 0.25 mm
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.520.7W.A.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P0K1.520.7W.A.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100170	P0K1.520.7W.B.010	10	





Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
<b>7W<sup>4)</sup> (Pt-wire, Ø 0.15 mm)</b>							
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	On request	P1K0.161.7W.Y.007	7	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	101114	P1K0.161.7W.A.007	7	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	101115	P1K0.161.7W.B.007	7	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	On request	P1K0.161.7W.Y.010	10	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	100757	P1K0.161.7W.A.010	10	substrate thickness 0.25 mm
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100759	P1K0.161.7W.B.010	10	substrate thickness 0.25 mm
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.232.7W.Y.010	10	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100766	P1K0.232.7W.A.010	10	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100258	P1K0.232.7W.B.010	10	
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	1/10 F0.3 (class K)	100969	P0K1.308.7W.K.007	7	substrate thickness 0.25 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.1 (class Y)	100725	P1K0.308.7W.Y.007	7	substrate thickness 0.25 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.15 (class A)	100514	P1K0.308.7W.A.007	7	substrate thickness 0.25 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.3 (class B)	100432	P1K0.308.7W.B.007	7	substrate thickness 0.25 mm

3) Operating temperature range of -200 °C to +600 °C

4) Operating temperature range of -200 °C to +600 °C

5) 1/10 IEC 60751 in the range of +15 °C to +35 °C

## Additional documents

Application note

Document name:

ATP\_E



## Order Information

### Platinum Sensor - Secondary reference



#### Material

P = Platinum

#### TCR

= Pt 3840 ppm/K	G = Pt 3911 ppm/K
U = Pt 3750 ppm/K	W = Pt 3850 ppm/K (extended operating temperature range in class A)

#### Resistance in $\Omega$ at 0°C

#### Size in mm

#### Operating temperature range

1 = -50 °C to + 150 °C	6 = -200°C to + 600 °C
2 = -50 °C to + 200 °C	7 = -200 °C to + 750 °C
3 = -200 °C to + 300 °C	8 = -200 °C to + 850 °C
4 = -200 °C to + 400 °C	10 = -70 °C to + 1000 °C

#### Connections

S = SIL	FK = Flat wire customer specific
I = Insulated wire	SW = Perpendicular wire
K = Extended wire	L = Insulated stranded wire
W = Wire	E = Enameled Cu-wire
FW = Flat wire	SE = Perpendicular enamelled CU-wire

#### Tolerance class

A = IEC 60751 F0.15	K = Customer-specific
B = IEC 60751 F0.3	P = Pair
C = IEC 60751 F0.6	G = Group
Y = IEC 60751 F0.1	

#### Wire length in mm

#### Special

T = Substrate thickness 0.25 mm	M = Metallized backside
D = Substrate thickness 0.38 mm	U = Inverted welding
R = Round housing	S = Special
W = Sintered powder	

P OK1. 520. 6 W. A. 007. D



Innovative Sensor Technology IST AG • Stegrütistrasse 14 • 9642 Ebnat-Kappel • Switzerland  
+41 71 992 01 00 • [info@ist-ag.com](mailto:info@ist-ag.com) • [www.ist-ag.com](http://www.ist-ag.com)

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes or product specifications without previous announcement reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • All rights reserved.

