## INFRASOLID®



Data Sheet HISpower

HIS2000R-C300-6

TO-8 Thermal Infrared Emitter

### HIS2000R-C300-6

#### Thermal infrared emitter with CaF2 window, hermetically sealed


Our HIS2000R-C300-6 is a NiCr filament based thermal emitter in a TO8 package, with a gold plated reflector in a hermetically sealed package with a  $CaF_2$  window. This guarantees longterm stability. The shorter cap with a hight of 6 mm improves the optical signal performance.

**HISpower series** emitters have an integrated gold plated reflector that directs the radiation emitted from the rear to the front in order to achieve maximum efficiency. All our emitters offer minimum drift at constant resistance (Ohm). Infrasolids IR emitters are characterized by a very low temperature coefficient of electrical resistance. Therefore the hot resistance and the cold resistance are almost identical which eases the electrical control of the IR sources.

#### **Key features**



High radiant power



High efficiency



Hermetic housing

- Pulsable thermal black-body infrared source mounted in an industry standard TO-8 package.
- Patented nanostructured radiating element achieves up to 500% more detection signal!
- Lower radiating element temperature of 630 °C increases lifetime!
- High-quality filter windows guarantee considerably less drift. Leakage tested!
- Wide wavelength range enables a broad range of applications.


# innovative infrared sources for gas detection & spectroscopy


#### Main specifications

Parameter	HIS2000R-C300-6
Package	TO-8
Radiating element area	40 mm <sup>2</sup>
Radiating element emissivity	> 0.9
Radiating element temperature	630 °C at 2.5 W
Optical output power	up to 780 mW
Max. electrical power (DC)	2.5 W
Max. electrical voltage	3.8 V
Max. electrical current	660 mA
Electrical resistance	56 Ω
Modulation frequency*	4 Hz
Filter/Window	CaF <sub>2</sub> (glued)
Wavelength range	2 to 11 μm
Filling gas	N <sub>2</sub>


 $<sup>^{\</sup>ast}$  50 % modulation depth, square wave signal, 50 % duty cycle

#### Optical specifications







#### Radiating element temperature




#### Modulation depth




#### **Electrical specifications**





#### Window material transmissivity







#### Angular radiation distribution









#### Operating mode recommendation:

All our IR sources can be driven in electrical voltage, current or power regulated mode. The application decides whether the operating mode is DC or AC (pulsed). Depending on the drive mode and the applied electrical power the electrical resistance of the IR emitter can change over time. For highest measurement accuracy a power regulated mode is always recommended for thermal IR emitters. However, it is the most complex operating mode and not suitable in all applications.

For applications that require a small and low-cost driving circuit with a maximum stability we have a technical note with an adjustable low dropout voltage (LDO) regulator.

For further information please refer to: www.infrasolid.com/technicalnote

www.infrasolid.com

