

physical. chemical. biological.
















Platinum sensor with wires, ESD-optimized For high temperatures

Benefits & Characteristics

- Excellent long-term stability
- Low self-heating
- Fast response time

- Vibration and temperature shock resistant
- ESD-optimized design

Illustration¹⁾



Technical Data

Operating temperature range:	-200 °C to +600 °C
Nominal resistance:	1000 Ω at 0 °C
Characteristics curve:	3850 ppm/K
Long-term stability:	< 0.04 % at 1000 h at maximal operating temperature
Tolerance class (dependent on temperature range):	IEC 60751 F0.15 A (IST AG reference)
Connection:	Pt-cladded Ni-wire, \emptyset 0.2 mm (solderable, weldable, crimpable, brazeable), 10 mm long
Dimensions L x W x H / H2:	1.8 x 2.0 x 0.65 / 1.1 mm
Tolerance (chip):	L ± 0.2 mm, W ± 0.2 mm,H ± 0.1 mm, H2 ± 0.3 mm
Special:	ESD-optimized design acc. IEC/EN 61000-4-2

Product Photo



P1K0.202.6W.A.010_155773 1/2



physical. chemical. biological.











Description: Order code: Former main reference P1K0.202.6W.A.010 155773 100896

Additional Documents

Application Note:

Document name: ATP_E





P1K0.202.6W.A.010_155773