


POK1.202.3K.A.010 Platinum sensor with wires For low to medium temperatures

Benefits & Characteristics

- Excellent long-term stability
- Low self-heating
- Optimal price/performance ratio


Illustration¹⁾



Technical Data

Operating temperature range:	-200 °C to +300 °C	
Nominal resistance:	100 Ω at 0 °C	
Characteristics curve:	3850 ppm/K	
Long-term stability:	< 0.04 % at 1000 h at maximal operating temperature	
Tolerance class (dependent on temperature range):	IEC 60751 F0.15	A (IST AG reference)
Connection:	Ni-wire Au-coated, Ø 0.2 mm, 10 mm long	
Dimensions:	2 x 2 x 0.65 / 1.3 (L x W x H / H2 in mm)	
Tolerance (chip):	L ±0.2 mm, W ±0.2 mm,H ±0.1 mm, H2 ±0.3 mm	

Product Photo





physical. chemical. biological.



Order Information		
Description:	Item number:	Former main reference:
P0K1.202.3K.A.010	101156	010.02600
Additional Documents		
	Document name:	
	Document name.	
Application Note:	ATP_E	



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved