

physical. chemical. biological.













P0K1.516.7W.B.010


Platinum sensor with wires For very high temperatures

Benefits & Characteristics

- Excellent long-term stability
- Low self-heating
- Fast response time

- Vibration and temperature shock resistant
- Simple interchangeability

Illustration¹⁾



Technical Data

Operating temperature range:	-200 °C to +750 °C
Nominal resistance:	100 Ω at 0 °C
Characteristics curve:	3850 ppm/K
Long-term stability:	< 0.04 % at 1000 h at maximal operating temperature
Tolerance class (dependent on temperature range):	IEC 60751 F0.3 B (IST AG reference)
Connection:	Pt-wire, \emptyset 0.2 mm (solderable, weldable, crimpable, brazeable), 10 mm long
Dimensions:	5.0 x 1.6 x 0.65 / 1.3
Tolerance (chip):	L \pm 0.2 mm, W \pm 0.2 mm,H \pm 0.1 mm, H2 \pm 0.3 mm

Product Photo



P0K1.516.7W.B.010 1/2



physical. chemical. biological.











Order Information

Description: Item number: Former main reference: 010.00954 P0K1.516.7W.B.010 100513

Additional Documents

	Document name:
Application Note:	ATP_E



P0K1.516.7W.B.010 2/2