

physical. chemical. biological.













P1K0.232.6W.A.010


Platinum sensor with wires For high temperatures

Benefits & Characteristics

- Excellent long-term stability
- Low self-heating
- Fast response time

Vibration and temperature shock resistant

Illustration¹⁾



Technical Data

Operating temperature range:	-200 °C to +600 °C
Nominal resistance:	1000 Ω at 0 °C
Characteristics curve:	3850 ppm/K
Long-term stability:	< 0.04 % at 1000 h at maximal operating temperature
Tolerance class (dependent on temperature range):	IEC 60751 F0.15 A (IST AG reference)
Connection:	Pt-cladded Ni-wire, Ø 0.2 mm (solderable, weldable, crimpable, brazeable), 10 mm long
Dimensions:	2.2 x 2.0 x 0.65 / 1.1
Tolerance (chip):	L \pm 0.2 mm, W \pm 0.2 mm,H \pm 0.1 mm, H2 \pm 0.3 mm

Product Photo



P1K0.232.6W.A.010 1/2



physical. chemical. biological.













Order Information

Description: Item number: Former main reference: P1K0.232.6W.A.010 100256 010.00237

Additional Documents

	Document name:
Application Note:	ATP_E



P1K0.232.6W.A.010 2/2