



Order Information - 10K (Pt-wire, Ø 0.25 mm)

Size	Dimensions (L x W x H / H2; L _w in mm)	Product description
Nominal resistance: 200 Ω at 0 °C		
420	3.85 x 1.9 x 0.45 /0.75; 7	P0K2.420.10K.K.007.D.S
Order code		104078
<i>Former order code</i>		<i>310.00445</i>

Additional Documents

	Document name:
Application Note:	ATP_E



Order Information

Platinum Sensor

Secondary reference

Material

P = Platinum

TCR

= Pt 3770 ppm/K G = Pt 3911 ppm/K
U = Pt 3750 ppm/K W = Pt 3850 ppm/K (extended operating temperature range in class A)

Resistance in Ω at 0 °C

Size in mm

Operating temperature range

1 = -50 °C to +150 °C 6 = -200 °C to +600 °C
2 = -50 °C to +200 °C 7 = -200 °C to +750 °C
3 = -200 °C to +300 °C 8 = -200 °C to +850 °C
4 = -200 °C to +400 °C 10 = -70 °C to +1000 °C

Connection

S = SIL FK = flat wire customer-specific
I = insulated wire SW = perpendicular wire
K = customer-specific L = insulate stranded wire
W = wire E = enameled Cu-wire
FW = flat wire

Tolerance class

A = IEC 60751 F0.15 K = customer-specific
B = IEC 60751 F0.3 P = pair
C = IEC 60751 F0.6 G = group
Y = IEC 60751 F0.1

Wire length in mm

Special

T = substrate thickness 0.25 mm M = metallized backside
D = substrate thickness 0.38 mm U = inverted welding
R = round housing S = special
W = sintered powder

P OK2. 420. 10 K. K. 007. D



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved