

Capacitive Humidity Sensor P14-W



Humidity allrounder, -50 °C to +150 °C, 5.0 x 3.81 mm, 10 mm wires

Capacitive humidity sensor P14 with wires Linear characteristics and wide range of potential uses - ideal solution for universal measuring tasks in a wide variety of different applications.

Product Name: P14-W (150pF \pm 50pF)

■ 150pF \pm 50pF (at +23 °C and 30 % RH)

■ 0 % RH to 100 % RH

■ -50 °C to +150 °C

■ 5.0 x 3.81 x 0.4 mm

■ 5 s

■ Air/Gas

Product Old code: 040.00174

Product code: 150466

Product details

P14-W humidity sensor for various applications

Thanks to its linear characteristics and its wide range of potential uses, the IST AG P14-W humidity sensor is the ideal solution for universal humidity measuring tasks in a wide variety of different applications. The sensor is capable of measuring 0 % RH to 100 % RH (maximal dew point +85 °C) with a capacitance of 150 pF \pm 50 pF (wired) / 180 pF \pm 50 pF (SMD) (at 30 % RH and +23 °C) and operates within a temperature range of -50 °C to +150 °C.

Benefits & Characteristics of this humidity sensor

- High chemical resistance
- Very low drift
- Wide temperature range
- High humidity stability
- Resistance to condensation
- Fast recovery time

[Customer-specific sensor available upon request](#)

Alternative wires

The IST AG P14-W humidity sensor is available with CuP-SIL-wire post-plated with Sn, Au/Cu-wire or as SMD for automatic packaging as standard.

Quality

Consistent with the well-known, high-quality standards in Switzerland, IST AG is certified according to ISO 9001:2015 (quality) and ISO 14001:2015 (environment). Appropriate processes are part of our daily work. They are regularly audited and extended parallel to the growth of our company.

[> Read more](#)

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

10-49	CHF 17.60
-------	-----------

50-99	CHF 15.50
-------	-----------

100-150	CHF 14.30
---------	-----------

90