



innovative
Sensor
Technology

Thermal gas flow sensor FS7 in positioning housing



Flow range from 0 to 100 m/s, -20 °C to +150 °C, easy orientation in a flow channel

For measuring flow rates using a symmetrical heater design and having an excellent sensitivity and reproducibility. It has a plastic housing for fast mounting into a flow channel

Product Name: FS7.A.1L.195

□□□□ : Gas Flow

□□ : One direction (anemometric)

□□□□□□ : -20 °C to +150 °C

□□□□ : Plastic housing

□□□□ /□□ : 6.9 x 2.4 x 0.20 mm

□□□□ : Cu/Ag stranded wire, PTFE-insulated

Flow range CTA mode: 0/ms to 100 m/s

□□□□ **T63:** ~200 ms (jump from 0 to 10000 sccm)

□□□□ : 0.01 m/s

□□ : Ceramic

□□□□ : 3 pins, Cu/Ag-stranded wires, AWG30, PTFE-insulated, 195 mm long

Product Old code: 050.00217

Product code: 157213

Product details

Thermal gas flow sensor FS7 in positioning housing > Details

Product description FS7

The IST AG FS7 thermal mass flow sensors are the successors of the FS5 flow sensors and exhibit a symmetrical heater design and enhanced sensitivity. The FS7 flow sensor is applicable in gas and offer excellent long-term stability. The small thermal mass of the FS7 sensor provides a fast response time. Additionally, the standard FS7 sensor is also available with a housing which is easily implemented into various applications.

The IST AG FS7 flow sensors are optimal for measuring gas flow in various flow applications.

Benefits & Characteristics of the FS7 gas flow sensor

- Easy adaptation in various applications and housings
- Excellent long-term stability
- Simple signal processing
- Simple calibration
- Stable platinum technology
- Excellent reproducibility

[Customer-specific sensor available upon request.](#)

The online shop

Quantity (pieces)	Price (per piece)
-------------------	-------------------

5-49	CHF 35.54
------	-----------

50-99	CHF 28.22
-------	-----------

Quantity (pieces) Price (per piece)

100-150 CHF 24.98

☐ : **0**